

DC-DC轉換器快選表



DC-DC
模塊型快選表

應用	封裝	系列		功率	輸入電壓	輸出電壓	輸出穩壓	隔離電壓	工作溫度	尺寸 (長 x 寬 x 高 mm)	安規					
		圖片	型號													
光伏儲能產業	DIP		DDRH-15-P	15W	150~1500V	5V 12V 15V 24V	穩壓	4KVAC	-40~+80°C	76.2 x 50.8 x 25	  EAC/CE/ UKCA					
			DDRH-30-P	30W	150~1500V	12V 15V 24V 48V										
			DDRH-45-P	45W	150~1500V	12V 15V 24V 48V										
			DDRH-15-ST	15W	150~1500V	5V 12V 15V 24V										
			DDRH-30-ST	30W	150~1500V	12V 15V 24V 48V										
			DDRH-45-ST	45W	150~1500V	12V 15V 24V 48V										
			DDRH-15-DR	15W	150~1500V	5V 12V 15V 24V										
			DDRH-30-DR	30W	150~1500V	12V 15V 24V 48V										
			DDRH-45-DR	45W	150~1500V	12V 15V 24V 48V										
	----	----		DDRH-60	60W	150~1500V	5V 12V 24V 48V	----	4KVAC	-30~+80°C	57 x 93.5 x 105	  CSA/EAC/ CE/UKCA				
	----	----		DDRH-120	120W	250~1500V	12V 24V 32V 48V	----					4KVAC	-40~+80°C	63 x 125.2 x 115	  CSA/ DEKRA/ EAC/CB/ CE/UKCA
	----	----		DDRH-240	240W	250~1500V	12V 24V 32V 48V	----					4KVAC	-40~+80°C	85.5 x 125.2 x 129.2	
	----	----		RSDH-150	150W	250~1500V	12V 24V 32V 48V	----	4KVAC	-40~+80°C	191 x 86 x 41	CSA/ DEKRA/ EAC/CB/ CE/UKCA				
	----	----		RSDH-300	300W	250~1500V	12V 24V 32V 48V	----					4KVAC	-40~+80°C	237 x 86 x 41	