

## ■ Features

- 5"×3" miniature size
- Universal AC input / Full range
- Built-in active PFC function
- EMI Class B for Class I & Class A for Class II configuration
- No load power consumption<0.5W by PS\_ON control
- High efficiency up to 94%
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Cooling by free air convection for 250W and 400W with 25CFM forced air
- Built-in 12V/0.5A FAN supply
- Standby 5V@1A with fan , 0.6A without fan
- Built-in remote sense function
- LED indicator for power on
- Output 18V available
- Operating altitude up to 5000 meters
- 3 years warranty

## ■ Applications

- Industrial automation machinery
- Industrial control system
- Mechanical and electrical equipment
- Electronic instruments, equipments or apparatus


## ■ GTIN CODE

MW Search : <https://www.meanwell.com/serviceGTIN.aspx>

## ■ Description

EPP-400 is a 400W highly reliable green PCB type power supply with a high power density on the 5" by 3" footprint. It accepts 80~264VAC input and offers various output voltages between 12V and 48V. The working efficiency is up to 94% and the extremely low no load power consumption is down below 0.5W. EPP-400 is able to be used for both Class I (with FG) and Class II(no FG) system design. EPP-400 is equipped with complete protection functions; it is complied with the international safety regulations such as TUV BS EN/EN62368-1, TUV BS EN/EN60335-1, UL62368-1 and IEC62368-1. EPP-400 series serves as a high price-to-performance power supply solution for various industrial applications.


## ■ Model Encoding




**SPECIFICATION**

| MODEL                 |   | EPP-400-12   | EPP-400-15   | EPP-400-18   | EPP-400-24   | EPP-400-27   | EPP-400-36   | EPP-400-48   |        |
|-----------------------|---|--|--------------|--------------|--------------|--------------|--------------|--------------|--------|
| OUTPUT                | DC VOLTAGE  | 12V  | 15V          | 18V          | 24V          | 27V          | 36V          | 48V          |        |
|                       | CURRENT   | 25CFM  | 33.3A        | 26.7A        | 22.3A        | 16.7A        | 14.9A        | 11.2A        | 8.4A   |
|                       |   | Convection   | 20.8A        | 16.7A        | 13.9A        | 10.5A        | 9.3A         | 7A           | 5.3A   |
|                       | RATED POWER   | 25CFM  | 399.6W       | 400.5W       | 401.4W       | 400.8W       | 402.3W       | 403.2W       | 403.2W |
|                       |   | Convection   | 249.6W       | 250.5W       | 250.5W       | 252W         | 251.1W       | 252W         | 254.4W |
|                       | RIPPLE & NOISE (max.) Note.2  | 120mVp-p   | 150mVp-p     | 180mVp-p     | 200mVp-p     | 200mVp-p     | 250mVp-p     | 250mVp-p     |        |
|                       | VOLTAGE ADJ. RANGE(MAIN OUTPUT)   | 11.4~12.6V   | 14.3~15.8V   | 17.1~18.9V   | 22.8~25.2V   | 25.6 ~ 28.4V | 34.2 ~37.8V  | 45.6 ~50.4V  |        |
|                       | VOLTAGE TOLERANCE Note.3  | ±3.0%  | ±3.0%        | ±3.0%        | ±2.0%        | ±1.0%        | ±1.0%        | ±1.0%        |        |
|                       | LINE REGULATION   | ±0.5%  | ±0.5%        | ±0.5%        | ±0.5%        | ±0.5%        | ±0.5%        | ±0.5%        |        |
|                       | LOAD REGULATION   | ±1.0%  | ±1.0%        | ±1.0%        | ±1.0%        | ±1.0%        | ±1.0%        | ±1.0%        |        |
| SETUP, RISE TIME      | 1000ms, 30ms/230VAC    1500ms, 30ms/115VAC at full load   |  |              |              |              |              |              |              |        |
| HOLD UP TIME (Typ.)   | 16ms/230VAC    12ms/115VAC at full load   |  |              |              |              |              |              |              |        |
| INPUT                 | VOLTAGE RANGE Note.4  | 80 ~ 264VAC  |              | 113 ~ 370VDC |              |              |              |              |        |
|                       | FREQUENCY RANGE   | 47 ~ 63Hz  |              |              |              |              |              |              |        |
|                       | POWER FACTOR  | PF>0.94/230VAC PF>0.98/115VAC at full load   |              |              |              |              |              |              |        |
|                       | EFFICIENCY (Typ.)   | 91.5%  | 92%          | 93%          | 93%          | 93.5%        | 93%          | 94%          |        |
|                       | AC CURRENT (Typ.)   | 4.2A/115VAC  |              | 2.1A/230VAC  |              |              |              |              |        |
|                       | INRUSH CURRENT (Typ.)   | COLD START 40A/115VAC  |              | 80A/230VAC   |              |              |              |              |        |
|                       | LEAKAGE CURRENT   | <0.75mA / 240VAC   |              |              |              |              |              |              |        |
| PROTECTION            | OVERLOAD  | 105 ~ 135% rated output power<br>Protection type : Hiccup mode, recovers automatically after fault condition is removed  |              |              |              |              |              |              |        |
|                       | OVER VOLTAGE  | 13.2 ~ 15.6V   | 16.5 ~ 19.5V | 19.8 ~ 23.4V | 26.4 ~ 31.2V | 29.7 ~ 35.1V | 39.6 ~ 46.8V | 52.8 ~ 62.4V |        |
|                       | OVER TEMPERATURE  | Protection type : Shut down o/p voltage, recovers automatically after temperature goes down  |              |              |              |              |              |              |        |
| FUNCTION              | 5V STANDBY  | 5VSB : 5V@0.6A without fan, 1A with fan 25CFM ; tolerance ±2%, ripple : 120mVp-p(max.)   |              |              |              |              |              |              |        |
|                       | FAN SUPPLY  | 12V@0.5A for driving a fan ; tolerance -15% ~+10% at main output 35% rated current (25CFM)   |              |              |              |              |              |              |        |
|                       | PS-ON INPUT SIGNAL  | Power on: PS-ON = "Hi" or " > 2 ~ 5V" ; Power off: PS-ON = "Low" or " < 0 ~ 0.5V"  |              |              |              |              |              |              |        |
|                       | POWER GOOD / POWER FAIL   | 500ms>PG>10ms ; The TTL signal goes high with 10ms to 500ms delay after power set up ; The TTL signal goes low at least 1ms before Vo below 90% of rated value |              |              |              |              |              |              |        |
| ENVIRONMENT           | WORKING TEMP.   | -30 ~ +70°C (Refer to "Derating Curve")  |              |              |              |              |              |              |        |
|                       | WORKING HUMIDITY  | 20 ~ 90% RH non-condensing   |              |              |              |              |              |              |        |
|                       | STORAGE TEMP., HUMIDITY   | -40 ~ +85°C, 10 ~ 95% RH   |              |              |              |              |              |              |        |
|                       | TEMP. COEFFICIENT   | ±0.03%/°C (0 ~ 50°C)   |              |              |              |              |              |              |        |
|                       | OPERATING ALTITUDE Note.7   | 5000 meters  |              |              |              |              |              |              |        |
|                       | VIBRATION   | 10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes   |              |              |              |              |              |              |        |
| SAFETY & EMC (Note 5) | SAFETY STANDARDS  | UL62368-1, TUV BS EN/EN62368-1, BS EN/EN60335-1, IEC62368-1, CCC GB4943.1, EAC TP TC 004 approved  |              |              |              |              |              |              |        |
|                       | WITHSTAND VOLTAGE   | I/P-O/P:3KVAC    I/P-FG:2KVAC    O/P-FG:0.5KVAC  |              |              |              |              |              |              |        |
|                       | ISOLATION RESISTANCE  | I/P-O/P, I/P-FG:100M Ohms / 500VDC / 25°C/ 70% RH  |              |              |              |              |              |              |        |
|                       | EMC EMISSION  | Compliance to BS EN/EN55032 (CISPR32) Class B, BS EN/EN61000-3-2,-3, CCC GB17625.1, GB/T9254, EAC TP TC 020  |              |              |              |              |              |              |        |
|                       | EMC IMMUNITY  | Compliance to BS EN/EN61000-4-2,3,4,5,6,8,11, BS EN/EN55035, BS EN/EN61000-6-2, heavy industry level, EAC TP TC 020  |              |              |              |              |              |              |        |
| OTHERS                | MTBF  | 1395.2K hrs min.    Telcordia SR-332 (Bellcore) ; 194.1K hrs min.    MIL-HDBK-217F (25°C)  |              |              |              |              |              |              |        |
|                       | DIMENSION   | 127*76.2*35mm (L*W*H)  |              |              |              |              |              |              |        |
|                       | PACKING   | 0.39Kg; 36pcs/15Kg/0.96CUFT  |              |              |              |              |              |              |        |
| NOTE                  | <p>1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25 of ambient temperature.</p> <p>2. Ripple &amp; noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1 μ F &amp; 47 μ F parallel capacitor.</p> <p>3. Tolerance : includes set up tolerance, line regulation and load regulation.</p> <p>4. Derating may be needed under low input voltages. Please check the derating curve for more details.</p> <p>5. Touch current was measured from primary input to DC output.</p> <p>6. The power supply is considered a component which will be installed into a final equipment. All the Class I (with FG) EMC test are been executed by mounting the unit on a 360mm*360mm metal plate with 1mm of thickness. The Class II (without FG) EMC test is been executed by mounting the unit on a 130mm*86.6mm metal plate with 1mm of thickness. final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on <a href="https://www.meanwell.com/Upload/PDF/EMI_statement_en.pdf">https://www.meanwell.com/Upload/PDF/EMI_statement_en.pdf</a>)</p> <p>7. The ambient temperature derating of 3.5°C/1000m with fanless models and of 5°C/1000m with fan models for operating altitude higher than 2000m(6500ft).</p> <p>※ Product Liability Disclaimer : For detailed information, please refer to <a href="https://www.meanwell.com/serviceDisclaimer.aspx">https://www.meanwell.com/serviceDisclaimer.aspx</a></p> |  |              |              |              |              |              |              |        |


■ Block Diagram



■ Derating Curve




■ Output Derating VS Input Voltage



|                  |      |
|------------------|------|
| Without Fan Watt | 250W |
| With Fan Watt    | 400W |

**Mechanical Specification**

Unit:mm



AC Input Connector (CN1) : JST B3P-VH or equivalent

| Pin No. | Assignment | Mating Housing        | Terminal                       |
|---------|------------|-----------------------|--------------------------------|
| 1       | AC/L       | JST VHR or equivalent | JST SVH-21T-P1.1 or equivalent |
| 2       | No Pin     |                       |                                |
| 3       | AC/N       |                       |                                |

DC Output Connector (CN2,CN3)

| Pin No. | Assignment | Output Terminals  |
|---------|------------|---|
| CN2     | -V         | M3.5 Pan HD screw in 2 positions<br>Torque to 8 lbs-in(90cNm)max. |
| CN3     | +V         |   |

Function Connector(CN95): TKP DH2L-2X2 or equivalent

| Pin No. | Assignment | Mating Housing        | Terminal          |
|---------|------------|-----------------------|-------------------|
| 1       | 5VSB       | TKP DH2 or equivalent | TKP or equivalent |
| 2,4     | DC COM     |                       |                   |
| 3       | PS-ON      |                       |                   |

Function Connector(CN11): TKP DH2I-2X2 or equivalent

| Pin No. | Assignment | Mating Housing        | Terminal          |
|---------|------------|-----------------------|-------------------|
| 1       | -S         | TKP DH2 or equivalent | TKP or equivalent |
| 2       | +S         |                       |                   |
| 3       | DC COM     |                       |                   |
| 4       | PG         |                       |                   |

FAN Connector(CN12) : TKP 8812-2 or equivalent

| Pin No. | Assignment | Mating Housing         | Terminal               |
|---------|------------|------------------------|------------------------|
| 1       | DC COM     | TKP 2502 or equivalent | TKP 8811 or equivalent |
| 2       | +12V       |                        |                        |

⊥ Grounding Required

⚠ HS1,HS2,HS3,HS4 can not be shorted

- ⊗ Note: When the input voltage is AC 230V the model delivers EMI Class B for both conducted emission and radiated emission for the power supply, When the input voltage is AC110V the model delivers EMI Class B for conducted emission ,Class A for radiated emission for the power supply.  
It delivers Class A for conduced emission and radiated emission, when configured into Class II (without FG) system.

**Installation Manual**

Please refer to : <http://www.meanwell.com/webnet/search/InstallationSearch.html>