



Specification

LED Back-lit Flat Panel (P Series)




NOTES:

1. This specification for our custom manufacturing product specifications.
2. The right of final interpretation of this specification to Guangzhou LEDIA Lighting Co., Ltd

1. Descriptions

The P-series LED Flat Panel ceiling light is a high performance LED panel that uses a unique back-lit design to provide a longer lasting lighting solution that replaces traditional fluorescent lighting or low-end edge-lits found in offices, hospitals, schools and more.




2. Characteristics

- ◆ High light efficiency up to 144lm/w
- ◆ Light weight design (30% lighter than edge-lit flat panels).
- ◆ Post-painted white aluminum frame to fit any décor.
- ◆ Designed to easily fit into existing suspended T-bar ceilings or hang via aircraft cable (optional accessory).
- ◆ CCT: 4000K.

Model	Size(mm)	A(mm)	B(mm)	C(mm)
LD-PN-P032-40-SDY	600*600*53mm	600	600	53

3. Applications



4. Technical Parameters

Code	LD-PN-P032-40-SDY
Power (W)	32W
PF	\
Input Voltage (V)	DC360~400V(with MEANWELL driver)
Lumen output(LM)	4600
CCT (K)	4000
Driver + LED	HongLi
Dimming	\
UGR	\
CRI	>80
Beam Angle	120°
Material	Aluminum+ Steel plate+ PS
Operating Temperature	-20°C to 40°C
Humidity	10% - 90%
Installation	Recessed/ Surface mount
Certificate	CE CCC
Environment	Indoor
Warranty	5Years
Product Dimension(mm)	600*600*53

Notes: Lumen is based on the condition of Ta=25°C, with a tolerance of +/-10%.

5. Photometric Data

